# CHEMTRONICS® Technical Data Sheet

## **Cottontips™ Low Lint**

#### PRODUCT DESCRIPTION

The Cottontips™ Low Lint Swab consists of cotton fibers which are tightly wrapped around a wooden handle. Because of the tightly wrapped head, there is very little linting and particulates are minimized. These swabs have excellent absorbency, as well as high strength especially when saturated with water. This swab is designed for cleaning applications where absorbency is critical.

- Low Particulates
- Tightly wrapped head construction
- High strength , durable head for rigorous cleaning
- Low Linting
- Excellent absorbency capacity and rate
- Good solvent compatibility

### TYPICAL APPLICATIONS

The Cottontips™ Low Lint Swab can be used to:

- Clean equipment and machinery, especially in small crevices or openings
- Remove flux residues from PCBs
- Apply adhesives or cleaning fluids
- Absorb liquid chemical residues

### **COMPATIBILITY**

Cottontips<sup>™</sup> Low Lint Swabs are compatible with most common solvents such as isopropyl alcohol, methanol, and ketones such as acetone. The cotton head is also compatible with bases and weak or dilute acids.

**CT5000** 6" (15.2 cm) Handle

1000 swabs / bag

Head length/width: 0.19" x 0.63"

(4.8 mm x 16 mm)

RoHS/WEEE

**Status** 



## TECHNICAL AND APPLICATION ASSISTANCE

ITW Chemtronics provides a technical hotline to answer your technical and application related questions. The toll free number is: **1-800-TECH-401**.

#### **MANUFACTURED BY:**

ITW CHEMTRONICS®
8125 Cobb Center Drive
Kennesaw, GA 30152 USA
1-770-424-4888 REV. (06/06)

Chemtronics® is a registered trademarks of ITW Chemtronics. All rights reserved. Cottontips $^{TM}$  is a trademark of ITW Chemtronics. All rights reserved.

DISTR	ABUT	ED B	<b>Y</b> :

#### **AVAILABILITY**