

IPA STENCIL & CLEANING WIPES

70% IPA / 30 DI% Wipes

1608-100DSP | 1608-100FL | 1608-100R

Introduction

Lint-free, tear-resistant wipes saturated with 70% isopropyl alcohol and 30% deionized water (DI) for economical cleaning. The additional DI slows down dry time slightly, allowing more soak-in time for thicker and more difficult soils. Made of hydro-entangled polyester material. Ideal for surface cleaning, stencil and tool cleaning, and PCB cleaning.



Flip-Top tubs – 1608-100FL

- 5"x8" (127mm x 203mm)
- 100 wipes/tub, 12 tubs/cs
- Lid springs closed automatically
- Stop dry-out from open lids
- Eco-friendly — Reduces waste & emissions

Disposable tubs – 1608-100DSP

- 5"x8" (127mm x 203mm)
- 100 wipes/tub, 12 tubs/cs
- Non-woven polyester material
- Lower cost disposable tub

Refill rolls – 1608-100R

- 5"x8" (127mm x 203mm)
- 100 wipes/roll, sold only in box of 6 rolls
- Non-woven polyester material
- Fits both 1610-100FL and 1610-100DSP tubs
- Reduces scrap tubs & saves money

General Features / Benefits

- Ideal for general surface cleaning, stencil cleaning & PCB defluxing
- Additional soak-in time for thicker and more difficult soils
- Broad range of material compatibility
- Lint-free, tear-resistant wipes

Chemical Components

CHEMICAL NAME	CAS #
2-Propanol	67-63-0
Water	7732-18-5

Chemical Properties

PHYSICAL STATE.....	Saturated wipe
ODOR	Alcohol odor
pH	Neutral
PERCENT VOLATILE.....	100
VOC	599 g/l / 70%
BOILING POINT (IPA)	82°C (180°F)
FREEZING POINT (IPA).....	-88°C
FLASHPOINT (IPA)	11.7°C (53°F) TAG CC
SOLUBILITY IN WATER.....	Miscible
EVAPORATION RATE	2.0 (n-Butyl Acetate=1)

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

1608-100DSP	Disposable tubs - 5"x8" (127mm x 203mm) pop-up wipes, 100 wipes/tub, 12 tubs/cs
1608-100FL	Flip-Top tubs - 5"x8" (127mm x 203mm) pop-up wipes, 100 wipes/tub, 12 tubs/cs
1608-100R	Refills - 5"x8" (127mm x 203mm) replacement wipes fi t -100FL and -100DSP tubs, 100 wipes/roll, sold only in box of 6 rolls

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
ITW Contamination Control BV
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
info@itw-cc.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.